

INFINITY PHOTO-OPTICAL TS-160 LENS ASSEMBLY GUIDE

Body



- T2 NEUTRAL MT
- FOCUS RING
- IRIS CONTROL

Macro Pro



- 135mm LENS
- 4x MACRO
- PORTRAIT LENS

Micro HM



- 100mm LENS
- 16x MICRO
- DEEP FOCUS
- INF to ~20in

SFX-1



- 100mm LENS
- DEEP FOCUS
- INF to ~20in

SFX-2



- 50mm LENS
- DEEP FOCUS
- INF to ~6in

SFX-3



- 35mm LENS
- DEEP FOCUS
- INF to ~2in

SCREW LENS TO MAIN BODY

REFER TO ROADMAP INSTRUCTIONS FOR ADDITIONAL INFO

T2 PL Mount



Additional T2 Mounts

Sony
Canon
Nikon
Leica
Pentax
Lumix



INFINITY PHOTO-OPTICAL 45° and 90° PRISM ASSEMBLY GUIDE

Setup for 45° Prism and 90° Prism (Shown)

REFER TO ROADMAP INSTRUCTIONS FOR ADDITIONAL INFO

Micro HM



UNSCREW SPACER



SCREW ON PRISM



* Install 8mm Spacer

ASSEMBLED



SFX-1



* Install 5mm Spacer



SFX-2



* Install 5mm Spacer



SFX-3



* Install 8mm Spacer



Macro Pro



No Prisms Used

* Each Prism comes with 5mm and 8mm spacer

45° Prism



Assembled

90° Prism



Assembled

FlipR



Unlock Horizon Adjust To Level Image

